

# Soprano*ice*

PLATINUM

## THE POWER OF THREE

- LIMITED EDITION -

TRIO CLUSTERED DIODE TECHNOLOGY  
FOR LASER HAIR REMOVAL

3 Combined Wavelengths Covering the Optimal Spectrum

• Proven Safety Record • Virtually Painless • All Skin Types, Even Tanned Skin

**Alma**  
Lasers™

# As an integrated solution, Soprano ICE Platinum combines the benefits of all 3 wavelengths, achieving excellent results to any single-wavelength approach on its own.

Celebrating 10 years of award-winning success, Alma Lasers is proud to present **Soprano ICE Platinum**, a limited edition platform for 2016 featuring **trio clustered diode technology**. The Platinum edition combines 3 laser wavelengths into a single innovative handpiece, simultaneously targeting different tissue depths as well as anatomical structures within the hair follicle. By combining the absorption and penetration levels of three different wavelengths, along with the treatment coverage, comfort and low maintenance of the diode laser, Soprano ICE Platinum achieves the safest and most comprehensive hair removal treatment available today.

## TRIO CLUSTERED DIODE TECHNOLOGY

Soprano ICE Platinum offers the synergistic benefits of the 3 most effective wavelengths for hair removal, each targeting different structures within the hair follicle. The 3 main anatomical targets include the Bulge, Bulb and Papilla.

## ALEX 755NM WAVELENGTH


The Alexandrite wavelength offers more powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color- especially light-colored and thin hair. With more superficial penetration, the 755nm wavelength targets the Bulge of the hair follicle and is especially effective for superficially embedded hair in areas such as the eyebrows and upper lip.

## SPEED 810NM WAVELENGTH

The classic wavelength in laser hair removal, the 810nm wavelength, offers deep penetration of the hair follicle with high average power, a high repetition rate and a large 2cm spot size for fast treatment. The 810nm has a moderate melanin absorption level making it safe for darker skin types. Its deep penetration capabilities target the Bulge and Bulb of the hair follicle while moderate tissue depth penetration makes it ideal for treating the arms, legs, cheeks and beard.

## YAG 1064NM WAVELENGTH

The YAG 1064 wavelength is characterized by lower melanin absorption, making it a focused solution for darker skin types. At the same time, the 1064nm offers the deepest penetration of the hair follicle, allowing it to target the Bulb and Papilla, as well as treat deeply embedded hair in areas such as the scalp, arm pits and pubic areas. With higher water absorption generating a higher temperature, the incorporation of the 1064nm wavelength increases the thermal profile of the overall laser treatment for most effective hair removal.



THE POWER  
OF THREE



“ The combination of the 3 different wavelengths enables practitioners to achieve better efficacy and highest coverage by simultaneously reaching different anatomical depths. This is the first time such a comprehensive treatment can be performed with just a single applicator.” ”


*Joseph Lepselter*, VP Clinical Affairs Alma Lasers

## SHR™ BY ALMA LASERS

**SHR is Alma Laser's proprietary hair removal method used in clinics around the world. It is the only clinically proven method of laser hair removal that is virtually painless.**

The Soprano ICE Platinum incorporates Alma's SHR method, ensuring safe and comfortable hair removal. Rather than exposing hair follicles to a single high energy pulse which can cause trauma to the skin, SHR works by gradually heating the dermis to a temperature that effectively damages the hair follicles and prevents regrowth, while avoiding injury to the surrounding tissue. A high repetition rate of short pulses are delivered deep into the dermis, achieving high average power and therapeutically effective heat build-up.

The sweeping In-Motion™ technique of moving the applicator repeatedly over the treatment area ensures full coverage while ICE™ tech cools the skin surface - preventing superficial burns and allowing for virtually painless yet highly effective hair removal.





INNOVATIVE  
3-IN-1  
APPLICATOR




SUITABLE FOR ALL SKIN  
TYPES, INCLUDING  
TANNED SKIN



10 YEARS OF  
CLINICALLY PROVEN  
EFFECTIVENESS



NO CONSUMABLES



EASY TO OPERATE

**Alma Lasers GmbH**

Nordostpark 100-102  
90411 Nürnberg, Germany  
Tel: + 49 911 / 89 11 29-0  
Fax: + 49 911 / 89 11 29-99

info@almalasers.com

PBSP17021601

©2016 Alma Lasers Ltd. All rights reserved.

Alma, Alma Lasers, the Alma Lasers logo, ICE, In-motion, SHR, Soprano, the Soprano ICE logo, and Speed are either registered trademarks or trademarks of Alma Lasers Inc. in the United States and/or other countries.

[www.sopranoplatinum.com](http://www.sopranoplatinum.com)

Connect with  
Alma Lasers

